


THE WORLD'S FIRST TRULY COMPACT, 10 Hz HIGH ACCURACY GREENHOUSE GAS ANALYZER



Real-Time Continuous Ambient and Source Monitoring


- N_2O : <300 ppt, CO_2 : <250 ppb, CH_4 <1.2 ppb
- Ultra-high stability and accuracy
- Operation from 1 to 10 Hz
- GPS-enabled for the ideal time stamp reference
- Built-in WiFi, RS232, and optional analog out
- Low power consumption: <200 W at steady-state
- Low maintenance sensor due to robust optics and user-serviceable filters

Introducing **MIRA Ultra Deca** — the world's first compact, rapid, and ultra-fast trace gas analyzer. Built on Aeris' miniature laser-based sensor platform, the Ultra Deca delivers laboratory-grade sensitivity and accuracy within seconds, with a robust, low-drift optical core engineered for high-flow operation and minimal maintenance. Operating in the mid-infrared (MIR) for exceptional specificity, it's lightweight and energy-efficient for both fixed and mobile deployments. The Ultra Deca is designed to measure core greenhouse gases at 10 Hz, enabling high-speed quantification of emissions and rapid, field-ready trace gas analysis.


The **MIRA Ultra Deca** uses an absorption-based method to provide excellent linearity across an extraordinarily broad concentration range, typically spanning several orders of magnitude. Unlike conventional 10 Hz open-path systems that can struggle in precipitation (fog or rain), the Ultra Deca's closed-path cell with low optical reflectivity minimizes measurement interference. This design also reduces maintenance needs and extends instrument life by eliminating routine mirror cleaning or replacement.

Aeris Technologies offers a 10 Hz measurement in the following combinations:

- N_2O/CO_2
- CH_4
- CH_4/C_2H_6



A typical time series of the MIRA Ultra Deca N_2O/CO_2 analyzer collecting at 10Hz in ambient air showing remarkable stability for N_2O .



Allan deviation of N_2O showing sensitivity down to 10 ppt with a 1-minute average.

INDUSTRY-LEADING SUB PPB ACCURACY AND SENSITIVITY

Metric	Specification
Measurement Method	Mid-Infrared Direct Laser Absorption Spectroscopy
Sensitivity (σ) at 10 Hz	N ₂ O: <300 ppt / CO ₂ : <250 ppb
	CH ₄ : <1.2 ppb
	CH ₄ : <3 ppb / C ₂ H ₆ : <1 ppb
Temperature / Humidity	10-40° C, 10 to 95% RH (non-condensing)
Measurement Range*	N ₂ O: 2 ppb - 500 ppm / CO ₂ : 10 ppm - 10,000 ppm
	CH ₄ : 10 ppb - 6,000 ppm
	CH ₄ : 10 ppb - 6,00 ppm / C ₂ H ₆ : 1 ppb - 1,000 ppm
Response time / Flow Rate	95 msec (1/e refresh rate), >9.0 L/min (volumetric)
Size (analyzer only)	48.3 cm W (19.0") x 17.7 cm H (7.0") x 27.9.0 cm D (11.0")
Weight (analyzer only)	9 kg (19.8 lbs)
Voltage / Max Current (analyzer only)	100-240 VAC 0.5 A (50-60 Hz) 22 W at steady state, 47 W at startup
Interface / Outputs	Wi-Fi, USB-A, DB9 RS232, Ethernet (optional analog out)
Memory	32 GB (expandable)
Aquisition Rate	1 Hz - 10 Hz (selectable)

*Linear measurement range. Operational range configurable for specific applications.

Included:	
Rugged Shipping Case	Tablet
10 Hz GPS	110/240V Power Plug

Optional Accessories:	
Anemometer	
External pump	

MIRA Ultra Rackmount systems ensure stable, low-drift performance with a temperature- and pressure-controlled sensor core, delivering exceptional accuracy and reproducibility for simultaneous gas measurements. This stability extends calibration intervals and, in some cases, eliminates the need for calibration. The system features two programmable sampling ports for calibration, re-zeroing, or differential measurements, supporting a wide variety of applications.

Core Sensor Technology

MIRA series analyzers combine Aeris' patented multipass cell technology with mid-IR solid-state lasers and custom electronics to achieve superior sensitivity and accuracy in an extremely robust and compact platform. The proprietary sensor engine used in every MIRA analyzer uniquely achieves a long absorption path length in an extremely small volume resulting in a fast response time with reduced pumping and power requirements.




MIRA's compact optical core achieves a 13 meter path length in a 60 cc volume.

The Power of Mid-infrared

Spanning wavelengths from 2.5 to 5 micrometers (μm), the Aeris mid-IR technology achieves the same or superior short-term sensitivity as fragile NIR cavity-based techniques. The robust design of the mid-IR core is well suited for a wide range of applications including airborne analysis and environmental monitoring.

Mid-infrared vs near-infrared absorption line strength



Absorption spectrum of greenhouse gases across the IR. Absorption line strength is orders of magnitude stronger in the Mid-IR than NIR.



Aeris Technologies, Inc. provides ultrasensitive gas analyzers for trace gas monitoring applications. Aeris is redefining the state of the art in laser-based gas analysis systems, reaching unparalleled size, weight, power, and cost milestones.

Aeris Technologies, Inc. 26252 Eden Landing Road, Hayward CA 94545
PH 650.620-9421 FAX 9451
www.aerissensors.com

DOC# SPE-00041a

